



CSP01—Gloss Medium NT Clear

What is a Gloss Medium Used For? In the CFE Color System it is used as an enhancement product. When you add any Color Concentrate to the Gloss Medium, you have created a colored gloss glaze and are in control of the color intensity. It is a non-toxic clear glaze and can be used over design work. Depending on the ratio of Color Concentrate to Gloss Medium the technical application may vary.

- CSP01 is perfect to create the popular “*Designed for Bisque Detail Glazes*” The blend is 1 part color to 1 part Gloss Medium for a high pigment detailed glaze with very smooth brushability. These blends can be used for brush work or color blocking on 04 bisque which is then covered with 2 coats of CSP01 Gloss Medium NT clear glaze and fired to cone 06.
- CSP01 Gloss Medium can be used as a base for creating a colored gloss glaze. The typical blend ratio is 4 parts CSP01 Gloss Medium NT clear to 1 part Color Concentrate. This creates a 3 to 4 coat gloss glaze. Fire to witness cone 06. Can be mixed 50/50 with CC's, decorate on cone 6 greenware and fire to cone 6.



Gloss Medium + Color Concentrates on China Blanks

- Mix 50/50 CSP01 Gloss Medium with Color Concentrate of choice.
- Stroke on design on China Blank
- Outlining and detailing a design is easily accomplished when staying on top of areas that you have stroked on. This gives it something to adhere to.
- If outline goes off design area onto the china surface it will be lighter in color.



What is Gloss Glaze Medium?

It is a glaze base for all intents and purposes. It contains frit, as well as other oxides and has been refined and ball milled for a smooth blend and brush consistency.

- It is Clear in Value.
- It is Non-Toxic.
- It does not Flow during firing.
- Currently Firing Range is Cone 04-6.
- Can be used as a Clear Glaze.
- When blended with any of the Color Concentrates it produces a food safe surface.



Colored Gloss Glaze

- Mix 4 parts CSP01 Gloss Medium with 1 part Color Concentrate CC152 Deep Cerulean.
- This creates a non-moving colored gloss glaze.
- 3-4 coat application needed



Colored Glaze Strokes

- Mix equal parts CSP01 Gloss Medium with Color Concentrate.
- Do brushstrokes on ware.
- Brush on 2 coats of CSP01 Gloss Medium NT Clear glaze.



China Blanks from **Vir-ma**